

## MJP EasyClean System

For the ProJet® MJP 2500 Series\*





- Convenient, fast and automatic turnkey removal of support material from plastic and elastomeric parts produced on Projet MJP 2500 3D printers
- Two warmer units (bulk wax remover and fine wax remover) use steam and EZ Rinse-C to melt wax supports away, without manual labor
- Intended to operate in a typical office environment, resting on a table, without objectionable noise or odor, and without requiring special ventilation or equipment, only requiring access to a sink

Features	MJP EasyClean System
Cleaning volume (w x d x h)	11.6 x 8.3 x 5.6 in (295 x 211 x 142 mm)
Electrical (specify at time of order)	100-120 VAC, 60 Hz, 15A, single phase 220-240 VAC, 50 Hz, 10A, single phase
Noise	<65 dBa
Weight Crated Uncrated	19 lb (8.6 kg) for warmers, 20.5 lb (9.3 kg) for accessory kit <25 lbs (11.3 kg) unfilled max (each) <35 lbs (15.9 kg) filled with water and accessories (each) >40 lbs (18.1 kg) when pans are full with wax or cleaning fluid
Dimensions (w x d x h) Crated Uncrated	25 x 17 x 12 in (635 x 432 x 305 mm) - each of 3 boxes 22 x 14 x 14 in (559 x 356 x 356 mm) - bulk and fine wax assembled with lids
Certifications	cTUVus, CE
Customer accessories kit (included)	2 pans, 3 lids, a strainer and strainer handles, Quick Start guide, appropriate country power cord

<sup>\*</sup> The MJP EasyClean System is sold separately

